EVERClassic

Traditional and Classical Design.



Fine Tips and Supple Curved Handle.



ver with

OU...



Orthodontic Pliers EVER Fine

*Traditional and classical design fascinate artistic mind. *Matte surface can avoid reflection of pliers under bright light.



-Bending Pliers-



Tweed Arch No.27455

*Maximum wire capacity .022"x.028" *Hold arch wire, apply torq, offsetbend, inset-bend




Three Jaw No.27457

*Maximum wire capacity .036" *Quad Helix, lingual arch, activate of main wire



-Utility Pliers-







8

*Insert, remove the main wire.

-Bending Pliers-





Tweed Loop Forming No.27456

Nance Closing Loop No.27459

*Maximum wire capacity .022"x.028" *Round beak is shaped 3 layers of cylinders (1.25mm, 1.85mm, 2.26mm in diameter) can be used for closing helical loop, helical loop, omega loop.

*Maximum wire capacity .022" *With using each step (3.5mm, 4.5mm, 5.5mm, 6.5mm), arrange the loop wire, apply torque on MEAW loop.

-Step Pliers-





-Banding Pliers-





Band Removing L No.27460

No.27458 *Maximum wire capacity .036" *Bend retainer wire, clasp.

458

Bird Beak

No.27454 *Maximum wire capacity .040" *Bend retainer wire, adjust inner bow with three steps. (1.4mm, 3.0mm, 4.5mm in diameter)

454


Young

8

445

Step 1/2mm

No.27445









453 Kim T/C (with Cutter) No.27453

*Maximum wire capacity .016"x.022" *Cut up to .020" *Bend MEAW loop.





452 Light Wire T/C (with Cutter) No.27452

- *Maximum wire capacity .020" *Cut up to .020"
- *Designed for circle hook, tear drop.

-Debonding Pliers-



444 Bracket Removing T/C No.27444







Orthodontic Pliers **EVER** Fine



Distal End Cutter EVER Fine

*Cut and hold distal end of arch wire.


*Cemented carbide inserts provide high performance and long life of the tips.

*Joint part has changed from 3pc(YS) to 2pc(EVER Fine). This change can reduce the problem of rust in joint part.





*Cut up to •Round wire .012"-.026" Rect. wire .016"x.016"-.022"x.028"



Sharp.3 616S T/C Sharp.3 616L T/C







YDM (Sharp.3 616L T/C • 606L T/C)



Company A *With long handle and small head to ensure easy access in hard to reach areas.


Size / 147mm

Sharp.3 616L T/C No.27617

606L T/C No.27607

*Cut up to •Round wire .012"-.026" Rect. wire .016"x.016"-.022"x.028"





606S T/C 606L T/C





Pin & Ligature Cutter EVER Classic



Pin & Ligature Cutter EVER Fine

*Cut excess ligature wire.

*Hard material inserts ensure cutting of ligature wire and elastic.

*Joint part has changed from 3pc(YS) to 2pc(EVER Fine). This change can reduce the problem of rust in joint part.




615 with Hard Material No.27615 *Cut up to .014" (ø0.35mm)

*To avoid breakage, insert hard material on the tip.

*Fine curved shape provide performance to cut ligature wire on crowded area, dislocated area easily.

 $^{\ast}10^{\circ}$ angle and fine curve allow easy to access both pre molars and molars.







605 with Hard Material No.27605 *Cut up to .012" (ø0.30mm)







Orthodontic Pliers EVER Fine

*With fine tips to ensure to insert into lingual or narrow part,crowded teeth. *With long handle to ensure to insert into lingual or narrow part,crowded teeth. *Matte surface can avoid reflection of pliers under bright light. *Supple curved handle fits female dentists.









451 Hole Punch No.27451

